


Pulsation Damper CIP, HPLC piggy-back PTFE and Polished stainless with Low Pressure CIP flushing

TuG-HPLC-TW TUBE GUARD "PiggyBack"
 Cleanable in place below pre-fill pressure. Pulse Damper



SANITARY / C.I.P. & HPLC DAMPER

CONNECTIONS "CB" OR "TRI-CLOVER" OR NATIONAL OR INTERNATIONAL DIARY FITTINGS UP TO 2" TUBING.



Item Pt #	DESCRIPTION	Mtrl.	Ht./Cast/PO #	CUSTOMER
1	9019c Type N2 Valve, Metal to Metal Seat	304ss		CUSTOMER Ref.
2	Gas Cap	Stainless PVQ Plant	SA240	3 Rd. Party QA \$s Extra
3	Liquid Chamber	Stainless PVQ Plant	SA240	DOCUMENTATION LEVEL \$s Extra
4	12 Boltings, Reduced to threat root Diameter	B8Mss		WELDING, W Nbr. 100% GTAW
5	Composite Diaphragm, PTFE + Elastomer	TFE-EPDM		SHOP / JOB Nbr.
6	Sealing, 90° shut-off PTFE on to polished ss			WEIGHT Est.
7	Anti-Extrusion Stiffener encapsulated in diaphragm			ISSUED By <i>TR</i> Date: / /
8	Connections, Tri-Clover, IDF, etc.			CHECKED By Date: / /
9	Transfer Fluid Set-Up port			FILE NAME
10	Cushion Chamber Gas Bag	Nitrile		SCALE NOT TO SCALE
11	Cover Plate Retaining Bolts	C.S.		REVISION Nbr. Date: / /
12	Cover Plate	316		DIMENSIONS: mm, Unless Otherwise Stated
13	Tamper-Proof Segmental Lock Ring	316		
14	Diametral Seal	Nitrile		
15	Cushion Gas End Plug	316L		
16	Piggy-Back Damper Body	316L		Sheet 1 of 1

PulseGuard "Y-T" Block Connection Options
 Provides an "O" ring and bolts interface between a pipe system and the damper capsule, ensures flo-thru pressure wave interception, in place flushability, saves flange and "T", 37.5° butt weld to system.

Called - Weld connection angles to this system fitting C/L

The PulseGuard "Top Hat" allows flushing of pipe crud, and pipe hydro-test before the damper capsule is bolted on, may also be used to replace the damper during service.

PulseGuard <http://www.PulseGuard.com>
<http://www.PulseGuard.co.uk>
PulseGuard für Deutschland www.pulsationdaempfer.com
PulseGuard, de langue Francaise amortisseurs-de-pulsations.com
PulseGuard, en Espanol / sud America amortiguador-de-pulsaciones.com
PulseGuard, dlya Russkogovoryaschih pulsations-dampfer.com

PulseGuard is the USA registered trade mark of PulseGuard Inc. PulseGuard is the UK registered trade mark of PulseGuard Ltd.
 UK --44(0)161-480-9625 USA ---1910-270-2737

PULSEGUARD
 For Americas & Pacific 01(1)910-270-2737
 For Europe & East --44(0)162-480-9625

VIEW NUMBER

Associate licensees:

- Shock Alleviators
- Flow Fuses
- Product Design
- Accumulators
- Analysis